



## Knurl forming tool left-hand, Shank size: 12mm



### Order data

Order number	290001 12
GTIN	4030741659676
Item class	29H

### Description

#### Version:

#### Top face of the shank = tip height

Grub screw in the shank for clearance angle correction.

Carbide roller pin for increased wear resistance.

**Click-Pin:** For quick and easy changing of the knurl.

### Technical description

Working range	3 - 50 mm
for knurl width w	4 mm
Shank height	12 mm
for knurl bore $\varnothing d_2$	4 mm
Shank width	12 mm
for knurl $\varnothing d_1$	10 mm
for knurl $\varnothing d_1$	15 mm
Roller pin	299910 1
for knurl profile	RBL 1×BR
for knurl profile	RAA 1×AA
for knurl profile	RGE30° 1×GV30°
for knurl profile	RGV30° 1×GE30°

for knurl profile	RBR 1×BL
Type of product	Self-centering knurling tool

---

## Accessories

Carbide roller pin Carbide Type 1	299910 1
-----------------------------------	----------