



## Knurl forming tool universal, Shank size: 20mm



### Order data

Order number	290004 20
GTIN	4030741317507
Item class	29H

### Description

#### Version:

#### Top face of the shank = tip height

Grub screw in the shank for clearance angle correction.

Carbide roller pin for increased wear resistance.

**Click-Pin:** For quick and easy changing of the knurl.

**Modular design:** Can be used as a right-hand or left-hand version.

### Technical description

for knurl $\varnothing d_1$	20 mm
for knurl $\varnothing d_1$	25 mm
Roller pin	299910 4
for knurl bore $\varnothing d_2$	6 mm
for knurl width w	8 mm
Shank height	20 mm
Working range	8 - 200 mm
Shank width	20 mm
Cutting direction	left-hand and right-hand
for knurl profile	RAA 1×AA
for knurl profile	RBL 1×BR

for knurl profile	RGV30° 1×GE30°
for knurl profile	RGE30° 1×GV30°
for knurl profile	RBR 1×BL
Type of product	Self-centering knurling tool

---

## Accessories

Carbide roller pinCarbide Type 4	299910 4
----------------------------------	----------