



## Cut knurling tool universal, Shank size: 16mm



### Order data

Order number	290200 16
GTIN	4030741663734
Item class	29H

### Description

#### Version:

**Modular design: Can be used universally as right-hand or left-hand version.**

Carbide running sleeve for increased wear resistance.

Quick tool adjustment by using the adjustment spindle.

Grub screw in the shank for clearance angle correction.

### Technical description

Carbide sleeve, cover disc, screw	299920 5
for knurl $\varnothing d_1$	15 mm
for knurl bore $\varnothing d_2$	8 mm
Working range	3 - 50 mm
Shank height	16 mm
Shank width	16 mm
for knurl width w	4 mm
Cutting direction	left-hand and right-hand
for knurl profile	RBL30° 1×AA
for knurl profile	RAA 1×BR30°
for knurl profile	RAA 1×BL30°

for knurl profile	RBR30° 1×AA
for knurl profile	RBR45° 1×BL15°
for knurl profile	RBL45° 1×BR15°
Type of product	Self-centering knurling tool

---

## Accessories

Spare parts kit (3 pieces), carbide bush, cover washer, screw Type 5	299920 5
--	----------