

Garant
Stub drill with 3 clamping faces HSS-E, uncoated, Ø DC h8: 1,5mm

Order data

| | |
|--------------|---------------|
| Order number | 113001 1,5 |
| GTIN | 4045197764805 |
| Item class | 11B |

Description
Version:

Stable and sturdy stub drill with **strengthened core diameter**. Ground flutes, with high concentricity. Precision ground point.

Recommendation:
Maximum drilling depth:

$$L_2 = L_c - 1.5 \times D_c$$

Note:

Drills with plain shank, **without drive flats**.

Technical description

| | |
|---|--------------|
| Tolerance nominal Ø | h8 |
| Feed f in steel < 900 N/mm ² | 0.03 mm/rev. |
| Shank Ø D _s | 1.5 mm |
| Flute length L _c | 9 mm |
| Number of cutting edges Z | 2 |
| Nominal Ø D _c | 1.5 mm |
| Standard | DIN 1897 |
| Overall length L | 32 mm |
| recommended maximum drilling depth L ₂ | 6.8 mm |
| Point angle | 130 degrees |
| Shank | Plain shank |

| | |
|-----------------|--------------|
| Coating | uncoated |
| Tool material | HSS E |
| Type | N |
| Through-coolant | no |
| Colour ring | without |
| Type of product | Jobber drill |

User data

| | Suitability | V _c | ISO code |
|--------------------------------|---|----------------|----------|
| Alu plastics | suitable only under restricted conditions | 70 m/min | N |
| Aluminium (short chipping) | suitable only under restricted conditions | 45 m/min | N |
| Alu > 10% Si | suitable only under restricted conditions | 40 m/min | N |
| Steel < 500 N/mm ² | suitable | 40 m/min | P |
| Steel < 750 N/mm ² | suitable | 30 m/min | P |
| Steel < 900 N/mm ² | suitable | 25 m/min | P |
| Steel < 1100 N/mm ² | suitable | 10 m/min | P |
| Steel < 1400 N/mm ² | suitable | 8 m/min | P |
| INOX < 900 N/mm ² | suitable | 12 m/min | M |
| INOX > 900 N/mm ² | suitable only under restricted conditions | 8 m/min | M |
| GG(G) | suitable only under restricted conditions | 25 m/min | K |
| CuZn | suitable only under restricted conditions | 80 m/min | N |
| Uni | suitable | | |
| Oil | suitable | | |
| wet maximum | suitable | | |

