

**Garant**
**Stub drill with 3 clamping faces HSS-E, uncoated, Ø DC h8: 2mm**

**Order data**

Order number	113001 2
GTIN	4045197764829
Item class	11B

**Description**
**Version:**

Stable and sturdy stub drill with **strengthened core diameter**. Ground flutes, with high concentricity. Precision ground point.

**Recommendation:**
**Maximum drilling depth:**

$$L_2 = L_c - 1.5 \times D_c$$

**Note:**

Drills with plain shank, **without drive flats**.

**Technical description**

Flute length $L_c$	12 mm
Tolerance nominal $\varnothing$	h8
Feed $f$ in steel < 900 N/mm <sup>2</sup>	0.03 mm/rev.
Number of cutting edges $Z$	2
Shank $\varnothing D_s$	2 mm
Overall length $L$	38 mm
Standard	DIN 1897
Nominal $\varnothing D_c$	2 mm
recommended maximum drilling depth $L_2$	9 mm
Point angle	130 degrees
Shank	Plain shank

Coating	uncoated
Tool material	HSS E
Type	N
Through-coolant	no
Colour ring	without
Type of product	Jobber drill

### User data

	Suitability	V <sub>c</sub>	ISO code
Alu plastics	suitable only under restricted conditions	70 m/min	N
Aluminium (short chipping)	suitable only under restricted conditions	45 m/min	N
Alu > 10% Si	suitable only under restricted conditions	40 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	40 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	30 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	25 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	10 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable	8 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	12 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable only under restricted conditions	8 m/min	M
GG(G)	suitable only under restricted conditions	25 m/min	K
CuZn	suitable only under restricted conditions	80 m/min	N
Uni	suitable		
Oil	suitable		
wet maximum	suitable		

