

Garant
Reducing adapter for PSC shank, SK 40, PSC inner: 4

Order data

Order number	301275 4
GTIN	4045197768919
Item class	31Z

Description
Version:

Ground internally and externally. The internal thread provided for the coolant tube in the PSC toolholder is plugged with the socket-head screw incorporated in the adapter. The clamping screw incorporates a through hole, so the system is suitable for internal coolant feed.

Application:

For adaption from SK to PSC.

Suitable for :

Tool arbor with **polygonal shank (PSC) – ISO 26623-1**.

Optional extras:

Pull studs (PS) No. 308600 – 308806. Pull stud wrenches No. 308820; 308835.

Concentricity: $\leq 3 \mu\text{m}$

Overhang dimension A: 30 mm

External \varnothing D: 40 mm

Length L: 11 mm

Technical description

Overhang dimension A	30 mm
External \varnothing D	40 mm
Length L	11 mm
Adapter	SK 40

Arbor standard	DIN 69871
Arbor standard	ISO 7388-1
Shape	ADB
Through-coolant	yes
Balance quality G at rotational speed	G 6.3 at 8,000 rpm
Concentricity	≤ 3 µm
Type of product	Arbor adapter

Accessories

Pull stud Mori-Seiki, sealed, form A suitable for steep tapers 40	308630 40
Pull stud 90° sealed suitable for steep tapers 40	308795 40
Torque insert for Pull studs to SO 7388 suitable for steep tapers 40 SK	308812 40
Pull stud Hurco 45° with fit sealed suitable for steep tapers 40	308802 40
Pull stud Mori-Seiki, sealed, form A suitable for steep tapers 40	308625 40
Special pull stud with internal thread suitable for steep tapers 40	308740 40
Pull stud stud sealed, form A suitable for steep tapers 40	308610 40
Pull stud 60° sealed suitable for steep tapers 40	308785 40
Pull stud Hurco 90° with fit sealed suitable for steep tapers 40	308806 40
Pull stud, 18CrNiMo7 sealed, form B suitable for steep tapers 40	308615 40
Special pull stud with no internal thread sealed suitable for steep tapers 40	308700 40
Pull stud sealed suitable for steep tapers 40	308635 40
Torque insert for Pull studs to DIN 69872 suitable for steep tapers 40 SK	308810 40

Wrench for pull studs ISO 7388 suitable for steep tapers 40 SK	308830 40
Pull stud Mazak sealed, form A suitable for steep tapers 40M	308670 40M
Special pull stud with no internal thread sealed suitable for steep tapers 40	308720 40
Pull stud Form A suitable for steep tapers 40	308600 40
Pull stud 90° sealed suitable for steep tapers 40	308790 40
Pull stud Form B suitable for steep tapers 40	308640 40
Pull stud sealed, form B suitable for steep tapers 40	308650 40
Pull stud sealed, form B suitable for steep tapers 40	308620 40
Pull stud sealed suitable for steep tapers 40	308660 40
Wrench for pull studs DIN ISO 7388-1 (formerly DIN 69872) suitable for steep tapers 40 SK	308820 40
Pull stud Hurco 45° with bore and fit sealed suitable for steep tapers 40	308801 40
Pull stud 45° sealed suitable for steep tapers 40	308765 40
Pull stud, 18CrNiMo7 Form A suitable for steep tapers 40	308605 40
Pull stud 45° sealed suitable for steep tapers 40	308760 40