

HOLEX®
VBMT 110304 Set 10 pieces, Grade: HBX020

Order data

Order number	261250 HBX020
GTIN	4045197766625
Item class	22D

Description

VBMT 110304 Set of 10 pieces HBX020 Grade: HBX020

Chip breaker: PM

Cutting depth a_p : 0.1 - 2.75 mm

Feed f : 0.1 - 0.25 mm/rev.

Cutting speed v_c main application: 80 - 300 m/min

Technical description

Corner radius	0.4 mm
Chip breaker	PM
Cutting depth a_p	0.1 - 2.75 mm
Feed f	0.1 - 0.25 mm/rev.
Grade	HBX020
Cutting conditions	slightly interrupted
Main application	P

Cutting speed v_c main application	80 - 300 m/min
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide
ISO code indexable insert	VBMT 110304
Number of changes/inserts	2
Type of product	Indexable insert for turning