


Garant
SNMM 120412, Grade: HB7020


Order data

Order number	251386 HB7020
GTIN	4045197766809
Item class	21G

Technical description

Cutting depth a_p	2 - 12 mm
Cutting conditions	slightly interrupted
Chip breaker	SR
Corner radius	1.2 mm
Grade	HB7020
Main application	P
Feed f	0.4 - 1.2 mm/rev.
Cutting speed v_c main application	100 - 300 m/min
Finishing/roughing assignment	Roughing
Tool material	Carbide
ISO code indexable insert	SNMM 120412

Number of changes/inserts	8
Type of product	Indexable insert for turning