

**Garant**
**Precision boring bar, DIN 1835 A, Nominal  $\varnothing$  D: 23,8mm**

**Order data**

Order number	236677 23,8
GTIN	4045197769268
Item class	21S

**Description**
**Application:**

For boring our pre-drilled or cast holes to the nominal  $\varnothing$  in combination with eccentric sleeve No. 236679.

For standard ISO indexable inserts CC..0602.

**Note:**

The  $\varnothing$  to be bored out must not be less than  $D_{\min}$ .

**Technical description**

Overall length $L_{\text{tot}}$	170 mm
suitable indexable insert	260142 HB725
Shank $\varnothing D_s$ h6	20 mm
Pack of insert screws	269440 (8IP; 1.2 Nm)
Minimum $\varnothing d_{\min}$	22 mm
Overhang $L_1$	37 mm
Adjustment range with eccentric clamping sleeve	23.5 - 24.3 mm
suitable eccentric clamping sleeve size No. 236679	20
Number of cutting edges Z	1
Nominal $\varnothing D$	23.8
Point angle	180 degrees
Shank type	DIN 1835 A

Through-coolant	yes
Type of product	Indexable drill

---

## Accessories

Torque screwdriver, fixed setting set torque 1,2 N·m	211750 1,2
PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 8IP	674252 8IP