

Cutting head, left-hand, System / insert size: DM/12



Order data

| | |
|--------------|---------------|
| Order number | 250028 DM/12 |
| GTIN | 4251414902459 |
| Item class | 29D |

Description

Version:

Interchangeable cutting heads for **vibration-damping base bodies**.

Application:

Vibration damping effect up a maximum overhang of **10×D**.

Through-coolant: yes

System: DM

ISO code indexable cutting head: DCLNR/L

suitable indexable insert: CN.. 1204..

suitable base body: 264910 – 264922

Minimum pre-drill $\varnothing D_{\min}$: 48 mm

Centre-line offset: 27 mm

Overall length: 35 mm

Technical description

| | |
|---------------------------------|----------|
| Shim | 259033 2 |
| ISO code indexable cutting head | DCLNR/L |
| Overall length | 35 mm |

| | |
|--|-----------------|
| suitable base body | 264910 – 264922 |
| Minimum pre-drill $\varnothing D_{\min}$ | 48 mm |
| System | DM |
| suitable indexable insert | CN.. 1204.. |
| Shim screw | 259027 2 |
| Centre-line offset | 27 mm |
| Clamp, screw, O-ring | 259036 3 |
| Insert size | 12 mm |
| Series | Cutting head |
| Application type | left-hand |
| Through-coolant | yes |

Accessories

| | |
|---|-------------|
| Clamp unit | 259505 |
| Shim | 259224 |
| Shim screw | 259612 |
| Torx® bit, shank E 6.3 Torx® profile TX10 | 674248 TX10 |
| Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cN·m | 659906 500 |