

Cutting head, left-hand, System / insert size: QC/11**Order data**

Order number	260409 QC/11
GTIN	4251414902640
Item class	29D

Description**Version:**

Interchangeable cutting heads for **vibration-damping base bodies**.

Application:

Vibration damping effect up a maximum overhang of **14xD**.

Through-coolant: yes

System: QC

ISO code indexable cutting head: SDUCR/L 11T3

suitable indexable insert: DC.. 11T3..

suitable base body: 264900 – 264908

Minimum pre-drill $\varnothing D_{\min}$: 26 mm

Centre-line offset: 15 mm

Overall length: 20 mm

Technical description

suitable base body	264900 – 264908
Minimum pre-drill $\varnothing D_{\min}$	26 mm
System	QC

Centre-line offset	15 mm
suitable indexable insert	DC.. 11T3..
ISO code indexable cutting head	SDUCR/L 11T3
Overall length	20 mm
Insert screw	269023 2
Insert size	11 mm
Series	Cutting head
Application type	left-hand
Through-coolant	yes

Accessories

Clamping screw	269432
Torx® bit, shank E 6.3 Torx® profile TX15	674248 TX15
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cN·m	659906 500