

Cutting head, left-hand, System / insert size: DM/16



Order data

Order number	251715 DM/16
GTIN	4251414902992
Item class	29D

Description

Version:

Interchangeable cutting heads for **vibration-damping base bodies**.

Application:

Vibration damping effect up a maximum overhang of **10×D**.

Through-coolant: yes

System: DM

ISO code indexable cutting head: DVUNR/L

suitable indexable insert: VNMG 1604..

suitable base body: 264910 – 264922

Minimum pre-drill $\varnothing D_{\min}$: 50 mm

Centre-line offset: 29 mm

Overall length: 35 mm

Technical description

Shim screw	259027 3
suitable indexable insert	VNMG 1604..
Centre-line offset	29 mm

ISO code indexable cutting head	DVUNR/L
Insert size	16 mm
Overall length	35 mm
System	DM
Minimum pre-drill $\varnothing D_{\min}$	50 mm
suitable base body	264910 – 264922
Shim	259033 5
Clamp, screw, O-ring	259036 7
Series	Cutting head
Application type	left-hand
Through-coolant	yes

Accessories

Shim screw	259613
Shim	259227
Clamp unit	259509
Torx® bit, shank E 6.3 Torx® profile TX15	674248 TX15
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cN·m	659906 500