

**Garant**
**HSS high-performance reamer HPC through hole, TiAlN, Nominal Ø DC: 32mm**

**Order data**

Order number	164358 32
GTIN	4045197769688
Item class	10N

**Description**
**Version:**

**Version suitable for NC** with straight shank Ø for the standardised toolholder, specially in **hydraulic chucks** or **high-accuracy chucks**.

This ensures **very high concentricity** and **process reliability**.

It is no longer necessary to procure special arbors.

With internal coolant feed for **HPC use** to reduce production costs.

With short, straight flutes.

**Tolerance specifications:**

**Configurable:** Reamers finish ground to match your specification.

**H7:** Version to DIN1420 for H7 bore tolerance.

**Application:**

For **HPC/HSC reaming** of **through holes**.

**Technical description**

Shank Ø D <sub>s</sub>	25 mm
Number of cutting edges Z	8
Overhang L <sub>1</sub>	139 mm
Nominal Ø D <sub>c</sub>	32 mm
Overall length L	200 mm
Feed f in steel < 1100 N/mm <sup>2</sup>	0.45 mm/rev.
Ø range	31.21 - 32.2 mm
Flute length L <sub>c</sub>	25 mm

Tolerance	Configurable
Reaming oversize in diameter	0.3 mm
Coating	TiAlN
Tool material	HSS
Standard	Manufacturer's standard
Through-coolant	yes, with 25 bar
Shank	DIN 6535 HA with h6
Machining strategy	HPC
Application for type of drilling	for through holes
Colour ring	green
Type of product	Phillips bit

## User data

	Suitability	V <sub>c</sub>	ISO code
Steel < 750 N/mm <sup>2</sup>	suitable	45 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	45 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	35 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable	35 m/min	P
GG	suitable	40 m/min	K
GGG	suitable	30 m/min	K
Uni	suitable		
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		