

Garant
Eccentric clamping sleeve, \varnothing d H5: 8mm

Order data

| | |
|--------------|---------------|
| Order number | 236679 8 |
| GTIN | 4045197768957 |
| Item class | 21P |

Description
Version:

Adjustment range in the $\varnothing \pm 0.5$ mm.

For use in conjunction with boring bars (No. 236677) -0.3 / +0.5 mm adjustment range to the nominal \varnothing .

Application:

Tool for boring to "fixed size" in conjunction with precision boring bar. Fitted in side lock arbors with Weldon shank \varnothing 25; 32 and 40 mm to DIN 1835 B.

Note:

The exact adjustment of the diameter is performed on the pre-setter by rotating the boring bar.

Technical description

| | |
|----------------------------------|-----------------|
| \varnothing d | 8 mm |
| Overall length L_{tot} | 62 mm |
| Tolerance external \varnothing | H5 |
| \varnothing D_1 | 29 mm |
| \varnothing D | 25 mm |
| L_1 | 57 mm |
| Type of product | Clamping sleeve |

