

Garant
HSS high-performance reamer HPC through hole, TiAlN, Nominal Ø DC: 26mm

Order data

Order number	164358 26
GTIN	4045197769626
Item class	10N

Description
Version:

Version suitable for NC with straight shank Ø for the standardised toolholder, specially in **hydraulic chucks** or **high-accuracy chucks**.

This ensures **very high concentricity** and **process reliability**.

It is no longer necessary to procure special arbors.

With internal coolant feed for **HPC use** to reduce production costs.

With short, straight flutes.

Tolerance specifications:

Configurable:Reamers finish ground to match your specification.

H7: Version to DIN1420 for H7 bore tolerance.

Application:

For **HPC/HSC reaming** of **through holes**.

Technical description

Flute length L_c	25 mm
Number of cutting edges Z	8
Nominal Ø D_c	26 mm
Overall length L	180 mm
Ø range	25.21 - 26.2 mm
Feed f in steel < 1100 N/mm ²	0.4 mm/rev.
Overhang L_1	125 mm
Shank Ø D_s	20 mm

Tolerance	Configurable
Reaming oversize in diameter	0.3 mm
Coating	TiAlN
Tool material	HSS
Standard	Manufacturer's standard
Through-coolant	yes, with 25 bar
Shank	DIN 6535 HA with h6
Machining strategy	HPC
Application for type of drilling	for through holes
Colour ring	green
Type of product	Phillips bit

User data

	Suitability	V _c	ISO code
Steel < 750 N/mm ²	suitable	45 m/min	P
Steel < 900 N/mm ²	suitable	45 m/min	P
Steel < 1100 N/mm ²	suitable	35 m/min	P
Steel < 1400 N/mm ²	suitable	35 m/min	P
GG	suitable	40 m/min	K
GGG	suitable	30 m/min	K
Uni	suitable		
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		