

Cutting head, right-hand, System / insert size: DM/12



Order data

Order number	250027 DM/12
GTIN	4251414902442
Item class	29D

Description

Version:

Interchangeable cutting heads for **vibration-damping base bodies**.

Application:

Vibration damping effect up a maximum overhang of **10×D**.

Through-coolant: yes

System: DM

ISO code indexable cutting head: DCLNR/L

suitable indexable insert: CN.. 1204..

suitable base body: 264910 – 264922

Minimum pre-drill $\varnothing D_{\min}$: 48 mm

Centre-line offset: 27 mm

Overall length: 35 mm

Technical description

Shim screw	259027 2
Insert size	12 mm
Minimum pre-drill $\varnothing D_{\min}$	48 mm

Shim	259033 2
Clamp, screw, O-ring	259036 3
ISO code indexable cutting head	DCLNR/L
System	DM
suitable base body	264910 – 264922
suitable indexable insert	CN.. 1204..
Centre-line offset	27 mm
Overall length	35 mm
Series	Cutting head
Application type	right-hand
Through-coolant	yes

Accessories

Shim	259224
Clamp unit	259505
Shim screw	259612
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cN·m	659906 500
Torx® bit, shank E 6.3 Torx® profile TX10	674248 TX10