

Boring bar base body vibration damped, 8×D, System / shank Ø: DM/40**Order data**

Order number	264920 DM/40
GTIN	4251414902114
Item class	29E

Description**Version:**

With cooling water connection 1/8-27 NPT.

Supplied with:

Reducing adaptor from G1/4 inch to G1/8 inch.

Note:

Do not clamp on the area marked **S**!

$D_{min} = 1/2 \text{ shank } \varnothing + H + \text{cutting head centre-line offset}$

Through-coolant: yes

System: DM

Overall length L_{tot} : 448 mm

non-clamping range S: 182.9 mm

recommended clamping length: 160 mm

Assembly bolt: 269025 1

Technical description

Shank Ø	40 mm
System	DM
Overall length L_{tot}	448 mm
non-clamping range S	182.9 mm
recommended clamping length	160 mm
Assembly bolt	269025 1
Boring depth up to	8×D
Vibration	damped

Through-coolant

yes

Accessories

Blade for hexagon, shank E 6.3 Hexagon 2 mm

674242 2

Torque screwdriver with scale, to take interchangeable
blades maximum torque 500 cN·m

659906 500