

## Cutting head, left-hand, System / insert size: QC/11



### Order data

Order number	260406 QC/11
GTIN	4251414902619
Item class	29D

### Description

#### Version:

Interchangeable cutting heads for **vibration-damping base bodies**.

#### Application:

Vibration damping effect up a maximum overhang of **14xD**.

Through-coolant: yes

System: QC

ISO code indexable cutting head: SDQCR/L 11T3

suitable indexable insert: DC.. 11T3..

suitable base body: 264900 – 264908

Minimum pre-drill  $\varnothing D_{\min}$ : 26 mm

Centre-line offset: 15 mm

Overall length: 22 mm

### Technical description

Minimum pre-drill $\varnothing D_{\min}$	26 mm
suitable indexable insert	DC.. 11T3..
System	QC

ISO code indexable cutting head	SDQCR/L 11T3
suitable base body	264900 – 264908
Insert size	11 mm
Centre-line offset	15 mm
Overall length	22 mm
Insert screw	269023 2
Series	Cutting head
Application type	left-hand
Through-coolant	yes

---

## Accessories

Clamping screw	269432
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cN·m	659906 500
Torx® bit, shank E 6.3 Torx® profile TX15	674248 TX15