



NC high-pressure vice, Type: 130



Order data

Order number	360535 130
GTIN	4045197772947
Item class	32P

Description

Version:

Sturdy base body of spheroidal cast iron, slides and base area hardened and ground. Fully enclosed spindle, spindle chamber enclosed with seals. Maximum clamping pressure reproducible using integral fixed stop.

- **Flatness of the base body ≤ 0.01 mm.**
- **With mechanical power intensifier, clamping pressure pre-selectable in 5 steps.**
- **Tapped holes in the side for workpiece backstops.**

Application:

Versatile clamping unit for machining centres.

Supplied with:

2 stepped jaws, 1 crank handle AF 14, 1 hexagon L-wrench and 4 table clamps.

Note:

Alignment dimensions not compatible with those of other manufacturers.

Technical description

t	79 mm
Clamping range d	66 - 315 mm
Weight	40 kg
r	111 mm
Colour code for suitable accessories	NC-HOLEX

Clamping range b	0 - 256 mm
Longitudinal slot l H7	20 mm
Base body length a	410 mm
Clamping force up to maximum	50 kN
Cross-slot n H7	20 mm
Base body height c	95 mm
Jaw height h	52 mm
m	139 mm
Overall length L	516 mm
Base body width B	131 mm
Series	NC
Type of product	Machine vice

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/360535-130>