

## Garant

### Solid carbide HPC drill Weldon shank DIN 6535 HB, TiAlN, Ø DC h7: 5,2mm



#### Order data

Order number	123115 5,2
GTIN	4045197401694
Item class	11E

#### Description

##### Version:

Cutting chisel edge with **high centring accuracy** due to **strong core and special point geometry**.

Particularly high alignment accuracy due to **4 guide chamfers** which stabilise the drill even at extreme depths!

**Straight major cutting edges** with honed edges and special flute profile for **short chips**, even on long chipping materials.

##### Advantage:

**High process reliability and surface quality of the hole.**

##### Note:

Flute length  $L_c = L_2 + 1.5 \times D_c$ .

#### Technical description

Feed f in stainless steel < 900 N/mm <sup>2</sup>	0.12 mm/rev.
Nominal Ø D <sub>c</sub>	5.2 mm
Number of cutting edges Z	2
Flute length L <sub>c</sub>	62 mm
Shank tolerance	h6
Tolerance nominal Ø	h7
Shank Ø D <sub>s</sub>	6 mm
Overall length L	100 mm
Standard	Manufacturer's standard

recommended maximum drilling depth $L_2$	54.2 mm
Coating	TiAlN
Tool material	Solid carbide
Version	10xD
Point angle	135 degrees
Shank	DIN 6535 HB to h6
Through-coolant	yes, with 25 bar
Machining strategy	HPC
Semi-Standard	yes
Colour ring	blue
Type of product	Jobber drill

## User data

	Suitability	$V_c$	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	200 m/min	N
Alu > 10% Si	suitable only under restricted conditions	180 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	110 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	80 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	70 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	65 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable	55 m/min	M
Ti > 850 N/mm <sup>2</sup>	suitable	25 m/min	S
Uni	suitable only under restricted conditions		
wet maximum	suitable		
wet minimum	suitable		

