

Cutting head, right-hand, System / insert size: DM/08



Order data

Order number	251918 DM/08
GTIN	4251414903005
Item class	29D

Description

Version:

Interchangeable cutting heads for **vibration-damping base bodies**.

Application:

Vibration damping effect up a maximum overhang of **10×D**.

Through-coolant: yes

System: DM

ISO code indexable cutting head: DWLNR/L 08

suitable indexable insert: WN.. 0804..

suitable base body: 264910 – 264922

Minimum pre-drill $\varnothing D_{\min}$: 48 mm

Centre-line offset: 27 mm

Overall length: 35 mm

Technical description

suitable indexable insert	WN.. 0804..
ISO code indexable cutting head	DWLNR/L 08
Insert size	8 mm

Overall length	35 mm
Minimum pre-drill $\varnothing D_{\min}$	48 mm
System	DM
Clamp, screw, O-ring	259036 5
Shim	259033 6
Centre-line offset	27 mm
Shim screw	259027 4
suitable base body	264910 – 264922
Series	Cutting head
Application type	right-hand
Through-coolant	yes

Accessories

Shim	259228
Shim screw	259614
Clamp unit	259507
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cN·m	659906 500
Torx® bit, shank E 6.3 Torx® profile TX10	674248 TX10