

Cutting head, right-hand, System / insert size: DM/15



Order data

Order number	250617 DM/15
GTIN	4251414902671
Item class	29D

Description

Version:

Interchangeable cutting heads for **vibration-damping base bodies**.

Application:

Vibration damping effect up a maximum overhang of **10×D**.

Through-coolant: yes

System: DM

ISO code indexable cutting head: DDUNR/L 15

suitable indexable insert: DNMG 1506..

suitable base body: 264910 – 264922

Minimum pre-drill $\varnothing D_{\min}$: 48 mm

Centre-line offset: 27 mm

Overall length: 35 mm

Technical description

Centre-line offset	27 mm
suitable base body	264910 – 264922
Clamp, screw, O-ring	259036 4

System	DM
suitable indexable insert	DNMG 1506..
Overall length	35 mm
Minimum pre-drill $\varnothing D_{\min}$	48 mm
Insert size	15 mm
Shim	259033 3
ISO code indexable cutting head	DDUNR/L 15
Shim screw	259027 2
Series	Cutting head
Application type	right-hand
Through-coolant	yes

Accessories

Clamp unit	259506
Shim	259225
Shim screw	259612
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cN·m	659906 500
Torx® bit, shank E 6.3 Torx® profile TX10	674248 TX10