

Garant
Solid carbide milling cutter TPC, DLC, Ø h6 DC: 16mm

Order data

Order number	202282 16
GTIN	4045197773265
Item class	11X

Description
Version:

Eccentric relief ground, additionally **polish ground** in the flutes for **outstanding chip evacuation** in long-chipping aluminium workpieces.

With double chip-breaker for exemplary chip formation.

With the latest generation of **DLC coating sp²**.

Note:

$a_{e \max} = 0.12 \times D$ for TPC machining.

h_{\max} : The values stated in the table are maximum values.

NEW GENERATION AVAILABLE! Recommended successor product is No. 203114.

Technical description

Shank Ø D_s	16 mm
Shank form	HB
Shank	DIN 6535 HB to h6
No. of teeth Z	3
Overall length L	132 mm
Flute length L_c	65 mm
Cutting edge Ø D_c	16 mm
Tolerance nominal Ø	h6
Direction of infeed	horizontal, oblique and vertical
Corner chamfer width at 45°	0.2 mm

Overhang length L_1 incl. recess	80 mm
Balance quality with shank	G 2.5 with HB
Recess $\varnothing D_1$	15 mm
Average chip thickness h_{\max} for TPC milling in short-chipping aluminium	0.096 mm
Helix angle	45 degrees
Corner chamfer angle	45 degrees
Coating	DLC
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	W
Helix angle characteristic	unequal spacing
Cutting width a_e for milling operation	$0.12 \times D$
Through-coolant	no
Machining strategy	TPC
Colour ring	yellow
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Aluminium	Suitable	280 m/min	N
Aluminium (short chipping)	suitable	270 m/min	N
Alu > 10% Si	suitable	180 m/min	N
PMMA acrylic	suitable	125 m/min	N
PE-HD	Suitable	110 m/min	N
PA 66	Suitable	140 m/min	N
PEEK	suitable	90 m/min	N
PF 31	Suitable	80 m/min	N

PVDF GF20	suitable	125 m/min	N
POM GF25	Suitable	115 m/min	N
PA 66 GF30	suitable	105 m/min	N
PEEK GF30	suitable	90 m/min	N
PTFE CF25	suitable	110 m/min	N
Honeycomb sandwich	suitable only under restricted conditions	120 m/min	N
Cu	Suitable	80 m/min	N
CuZn	Suitable	100 m/min	N
wet maximum	suitable		
wet minimum	suitable		
dry	suitable only under restricted conditions		
Air	suitable only under restricted conditions		