

## Cutting head, left-hand, System / insert size: DM/15



### Order data

Order number	250618 DM/15
GTIN	4251414902695
Item class	29D

### Description

#### Version:

Interchangeable cutting heads for **vibration-damping base bodies**.

#### Application:

Vibration damping effect up a maximum overhang of **10xD**.

Through-coolant: yes

System: DM

ISO code indexable cutting head: DDUNR/L 15

suitable indexable insert: DNMG 1506..

suitable base body: 264910 – 264922

Minimum pre-drill  $\varnothing D_{\min}$ : 48 mm

Centre-line offset: 27 mm

Overall length: 35 mm

### Technical description

System	DM
suitable indexable insert	DNMG 1506..
Overall length	35 mm

Minimum pre-drill $\varnothing D_{\min}$	48 mm
Centre-line offset	27 mm
suitable base body	264910 – 264922
Shim	259033 3
ISO code indexable cutting head	DDUNR/L 15
Clamp, screw, O-ring	259036 4
Shim screw	259027 2
Insert size	15 mm
Series	Cutting head
Application type	left-hand
Through-coolant	yes

## Accessories

Shim screw	259612
Clamp unit	259506
Shim	259225
Torx® bit, shank E 6.3 Torx® profile TX10	674248 TX10
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cN·m	659906 500