

Garant

Solid carbide extension for screw-in milling cutters $\varnothing d = 32$ mm, Thread M \times L: M16X260


Order data

Order number	301368 M16X260
GTIN	4045197770936
Item class	31Z

Description
Version:

Solid carbide extension with vibration-damping properties, shank tolerance h6, long and slim version.

Application:

Particularly for use in shrink-fit chucks. Perfect combination of standard steel extensions and Densimet® extensions.

Technical description

External $\varnothing D$	29 mm
Bore $\varnothing D_1$	17 mm
Shank $\varnothing d$	32 mm
Overall length L_{tot}	260 mm
Thread M	M16
Reach L_1	200 mm
Adapter	$\varnothing d = 32$ mm
Through-coolant	yes
Vibration	damped
Type of product	Extension

