

Garant
Clamp toolholder, right-hand, Shank / insert size: 25/16mm

Order data

Order number	250016 25/16
GTIN	4045197771940
Item class	21T

Technical description

Head length L ₁	36 mm
ISO code toolholder	DCLNR/L 2525M16
Functional width L ₄	32 mm
Insert size	16 mm
Shim	259031 35
Clamp, screw, spring	259035 6
suitable indexable insert	CN.. 1606..
Shank size	25 mm
Overall length L	150 mm
Shim screw	259025 11
Series	QuickTurn
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	95 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Type of product	Boring bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 1600 cNm	659906 1600
Shim Type 35	259031 35
8 mm blade with magnet with 1/4 inch bit holder overall length 50 mm	659874 50
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX25	674248 TX25
Shim screw Type 11	259025 11
Torque screwdriver with scale, to take interchangeable blades maximum torque 1600 cNm	659957 1600