




## HOLEX Pro Steel solid carbide roughing end mill HPC, TiAlN, Ø DC: 15,6mm



### Order data

Order number	202414 15,6
GTIN	4045197776235
Item class	12X

### Description

#### Version:

For **roughing and finishing**.

Up to 1×D into solid material **at very high feed rates** with smooth cutting action.

#### Advantage:

Optimised flute form, eccentric relief ground, wide chip space.

### Technical description

Feed $f_z$ for side milling in steel < 900 N/mm <sup>2</sup>	0.1 mm
Direction of infeed	horizontal, oblique and vertical
Cutting edge Ø D <sub>c</sub>	15.6 mm
Corner chamfer width at 45°	0.4 mm
Overhang length L <sub>1</sub> incl. recess	44 mm
Flute length L <sub>c</sub>	32 mm
Recess Ø D <sub>1</sub>	15.1 mm
Shank	DIN 6535 HB to h6
Overall length L	92 mm
No. of teeth Z	3
Tolerance nominal Ø	0 / -0.03
Feed $f_z$ for slot milling in steel < 900 N/mm <sup>2</sup>	0.08 mm
Shank Ø D <sub>s</sub>	16 mm

Helix angle	45 degrees
Corner chamfer angle	45 degrees
Series	Pro Steel
Coating	TiAlN
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	N
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Cutting width $a_e$ for milling operation	0.4×D for side milling
Cutting width $a_e$ for milling operation	Full slot cutting depth 1×D
Through-coolant	no
Machining strategy	HPC
Colour ring	green
Type of product	End / face mill

## User data

	Suitability	$V_c$	ISO code
Steel < 500 N/mm <sup>2</sup>	suitable	240 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	220 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	170 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	150 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable only under restricted conditions	80 m/min	M
GGG	suitable	190 m/min	K
Uni	suitable		
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		

dry	suitable
Air	suitable