



## HOLEX Pro Steel solid carbide torus cutter HPC, TiAlN, Ø DC / R1: 4/1,0mm



### Order data

Order number	206357 4/1,0
GTIN	4045197770561
Item class	12X

### Description

#### Version:

Tolerance: Corner radius  $R_1 = \pm 0.03 \text{ mm}$ .

#### Advantage:

HPC milling cutters will with various corner radii for all radial transitions.  
Optimised flute form, eccentric relief ground, wide chip space.

### Technical description

Overall length L	57 mm
Cutting edge Ø D <sub>c</sub>	4 mm
Feed f <sub>z</sub> for side milling in steel < 900 N/mm <sup>2</sup>	0.025 mm
Flute length L <sub>c</sub>	11 mm
Shank Ø D <sub>s</sub>	6 mm
Overhang length L <sub>1</sub> incl. recess	15 mm
Corner radius R <sub>1</sub>	1 mm
Recess Ø D <sub>1</sub>	3.8 mm
No. of teeth Z	4
Feed f <sub>z</sub> for slot milling in steel < 900 N/mm <sup>2</sup>	0.02 mm
Shank	DIN 6535 HB to h6
Helix angle	38 degrees
Series	Pro Steel

Coating	TiAlN
Tool material	solid carbide
Standard	Manufacturer's standard
Type	N
Tolerance nominal $\varnothing$	0 / -0.03
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Direction of infeed	horizontal, oblique and vertical
Cutting width $a_e$ for milling operation	Full slot cutting depth $1 \times D$
Cutting width $a_e$ for milling operation	Full slot cutting depth $1 \times D$
Through-coolant	no
Machining strategy	HPC
Colour ring	green
Type of product	Torus cutter

## User data

	Suitability	$V_c$	ISO code
Steel < 500 N/mm <sup>2</sup>	suitable	260 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	240 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	180 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	160 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable only under restricted conditions	80 m/min	M
GG(G)	suitable	250 m/min	K
Uni	suitable		
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		
dry	suitable		

Air

suitable