

Garant
eco screw-on toolholder, right-hand, Shank size / insert size: 20/16mm

Order data

Order number	261102 20/16
GTIN	4045197771889
Item class	21U

Description
Version:

With internal coolant feed right to the cutting edge. Cooling by means of precision nozzles effectively and efficiently reduces the thermal loading, since the coolant stream is optimally directed between the chip and cutting edge. This results in higher productivity, longer tool life and increased process reliability.

With flank face cooling.

Note:

Coolant transfer only in conjunction with GARANT eco-system toolholders No. 317900 – 319886.

Through-coolant: yes

ISO code toolholder: SVJBR/L 2020X16

suitable indexable insert: VB.. 1604..

Functional width L_4 : 25 mm

Head length L_1 : 40 mm

Overall length L: 99 mm

Pack of insert screws: 269023 3

Technical description

suitable indexable insert	VB.. 1604..
Overall length L	99 mm
Functional width L_4	25 mm
Insert size	16 mm
Shim	259033 5

Shank size	20 mm
Pack of insert screws	269023 3
Shim screw	269013 1
Head length L ₁	40 mm
ISO code toolholder	SVJBR/L 2020X16
Series	Eco
Application type	right-hand
Standard	DIN ISO 5610
Through-coolant	yes
Setting angle κ	93 °
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500