


LESSMANN®
THE GERMAN BRUSH COMPANY**Wheel brush with shank Stainless steel complete 0.20 mm, Brush Ø D1×
bristle width L1: 50X15mm****Order data**

Order number	574255 50X15
GTIN	4017359083857
Item class	57L

Description**Version:**

Waved special high quality wire, **shank Ø 6 mm.**
All components of stainless steel.

Application:

For portable grinders, on flexible drive machines or drills for brushing surfaces. High speeds improve the brush performance.
For removal of rust and scale, and for cleaning

Technical description

maximum speed	15000 min ⁻¹
Brush Ø D ₁	50 mm
Length of brush section H ₁	12 mm
Bristle thickness	0.2 mm
Bristle width L ₁	15 mm
Shank Ø D _s	6 mm

Type of product

Wheel brush