

LESSMANN®
THE GERMAN BRUSH COMPANY**Surface brush Steel wire 0.30 mm, Brush Ø D1: 60mm****Order data**

Order number	574750 60
GTIN	4017359116180
Item class	57L

Description**Version:**Area brushes with **shank Ø 6 mm.****Application:**

In straight die grinders, flexible shafts or on stationary machines. For cleaning and deburring small to medium-sized areas.

Technical description

maximum speed	8000 min ⁻¹
Brush Ø D ₁	60 mm
Length of brush section H ₁	25 mm
Bristle thickness	0.3 mm
Shank Ø D _s	6 mm
Type of product	End brush

