


**Base plate, for chuck type: 160mm****Order data**

| | |
|--------------|---------------|
| Order number | 313910 160 |
| GTIN | 5907412203706 |
| Item class | 36B |

Description**Version:**

Swivel base with longitudinal tenon slot for fast and exact alignment of the vice. Clamping slots for easy fitting to the machine table.

Application:

For attachment of lathe chucks with recessed mount to DIN 6350.

Supplied with:

T-nuts, fastening screws.

Technical description

| | |
|-------------------------|------------|
| Slot width S | 14 mm |
| Total weight | 4.8 kg |
| Height H | 28 mm |
| Width B | 190 mm |
| Aperture E | 90 mm |
| Pitch circle diameter F | 140 mm |
| Length A | 250 mm |
| Type of product | Base plate |

