



## High feed rate milling cutter 7792VX, with threaded shank, Ø D / number of teeth Z: 35/4mm



### Order data

Order number	221905 35/4
GTIN	4056544196644
Item class	28R

### Description

#### Description:

The unique design of the indexable inserts together with their approach angle in the milling body greatly reduces the radial forces and diverts them into the axial direction. Particularly thick indexable inserts with 4 cutting edges for the heaviest duties and high cost-effectiveness. The tool has particular advantages for face milling and milling deep pockets. With its ground wiper chamfer it is equally well suited also to plunge milling and finish milling operations.

### Technical description

Ø D <sub>3</sub>	20 mm
Insert screw	229918 (T15; 2.1 Nm)
Cutting edge Ø D <sub>c</sub>	35 mm
Indexable insert size	09
Number of cutting edges Z	4
Overall length L <sub>tot</sub>	43 mm
Mounting thread M	M16
maximum cutting depth a <sub>p max</sub>	1.5 mm
suitable indexable insert	XD.. 0904
Through-coolant	yes

Ramping length L for $\alpha_{\max}$	19.3 mm
Circular interpolation milling $\varnothing D_{\min}$	55 mm
Ramping angle $\alpha_{\max}$	0.74 degrees
Circular interpolation milling $\varnothing D_{\max}$	68 mm
Shank type	with threaded shank
Milling application	Ramping
Milling application	Circular milling
Milling application	Plunging
Machining strategy	HPC
Type of product	Copy mill

## Accessories

Clamping screw	229918
----------------	--------