

Garant

Revolving lathe centre for interchangeable heads., Morse taper: 5



Order data

Order number	320659 5
GTIN	4045197774378
Item class	31Z

Description

Version:

- **Punch axis of through-hardened steel mounted on shank bearings.**
- **Live centre through hardened, multiple regrinding possible.**
- **Precision roller bearings for high concentricity.**
- **Maintenance-free due to lifetime lubrication.**
- **Special seal prevents ingress of dirt and coolant.**
- **Complete tool hardened and ground.**

Description:

Lathe centres are mainly used on lathes to support long and slim workpieces, since with these workpieces there would otherwise be a risk of the workpiece bending or moving around as a result of the forces generated.

The lathe centre is secured with a Morse taper. The workpiece is clamped in the chuck and a counterbore is added using a centre drill. After re-clamping, the lathe centre is then inserted.

Application:

For all types of lathe, equally suitable for roughing and finish turning.

Flexible application thanks to exchangeable inserts. For general use on turrets and counter-spindles on CNC machines.

Optional extras:

Exchangeable inserts No. 320625 - 320631

Note:

Changing the inserts in the key surfaces by counter-rotation.

Body Ø D: 96 mm

maximum radial run-out: 0.005 mm

maximum speed: 2600 min⁻¹

for workpiece weight: 1100 kg

Length 1: 72 mm

L₂: 14 mm

Technical description

maximum radial run-out	0.005 mm
maximum speed	2600 min ⁻¹
Morse taper	MK5
for workpiece weight	1100 kg
Body Ø D	96 mm
suitable for colour code	K24
Length 1	72 mm
L ₂	14 mm
External Ø D ₁	24 mm
Shank Ø D ₂	42 mm
Type of product	Centring drill

Accessories

Insert for the revolving lathe centre Type 5	320631 5
Insert for the revolving lathe centre Type 6	320631 6
Insert for the revolving lathe centre Type 4	320631 4
Insert for the revolving lathe centre Type 3	320631 3
Insert for the revolving lathe centre Type 2	320631 2
Insert for the revolving lathe centre Type 1	320631 1