

**Garant**
**CNMG 120408, Grade: HB7010-1**


### Order data

Order number	250060 HB7010-1
GTIN	4045197779069
Item class	21G

### Description

CNMG 120408 HB7010-1 Grade: HB7010-1  
 Chip breaker: SS  
 Cutting depth  $a_p$ : 0.3 - 2.5 mm  
 Feed  $f$ : 0.1 - 0.4 mm/rev.  
 Cutting speed  $v_c$  main application: 150 - 500 m/min

### Technical description

Grade	HB7010-1
Feed $f$	0.1 - 0.4 mm/rev.
Cutting speed $v_c$ main application	150 - 500 m/min
Chip breaker	SS
Corner radius	0.8 mm
Cutting conditions	continuous
Cutting depth $a_p$	0.3 - 2.5 mm

Main application	P
Finishing/roughing assignment	Finishing
Tool material	Carbide
ISO code indexable insert	CNMG 120408
Number of changes/inserts	4
Type of product	Indexable insert for turning