

**Seaming tool, Jaw capacity: 55 mm****Order data**

Order number	861620 55
GTIN	4008158027050
Item class	83K

**Description****Version:**

Manual vacuum pumps for maximum suction force, and hence very high horizontal clamping force. Levers on the guide rails to compensate for differences in height. Engaging the handle on the suction cups generates a vacuum and the seaming tool adheres automatically to the sheet.

**Application:**

For clamping and positioning components with smooth surfaces, such as ceramic, granite, Corian®, plastic, sheet metal and glass.

**Note:**

The seaming tool should be released for storage, so that the rubber cups do not deform permanently.

See No. 086200 for suction lifters.

maximum clamping force: 260 N

overall length: 361 mm

**Technical description**

Jaw capacity	55 mm
maximum clamping force	260 N
overall length	361 mm
Weight	1.55 kg
Width	147 mm

Type of product

Clamp