

Garant
CNMG 120408, Grade: HB7010-1


Order data

Order number	250158 HB7010-1
GTIN	4045197779601
Item class	21G

Technical description

Feed f	0.2 - 0.5 mm/rev.
Grade	HB7010-1
Main application	P
Corner radius	0.8 mm
Cutting conditions	continuous
Chip breaker	SM
Cutting depth a_p	0.5 - 8 mm
Cutting speed v_c main application	120 - 440 m/min
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide
ISO code indexable insert	CNMG 120408

Number of changes/inserts	4
Tolerance	M
Type of product	Indexable insert for turning