

Garant
CNMG 120412, Grade: HB7010-1


Order data

Order number	250160 HB7010-1
GTIN	4045197779618
Item class	21G

Description

CNMG 120412 HB7010-1 Grade: HB7010-1
 Chip breaker: SM
 Tolerance: M
 Cutting depth a_p : 0.5 - 8 mm
 Feed f : 0.2 - 0.5 mm/rev.
 Cutting speed v_c main application: 120 - 440 m/min

Technical description

Cutting speed v_c main application	120 - 440 m/min
Main application	P
Cutting conditions	continuous
Grade	HB7010-1
Feed f	0.2 - 0.5 mm/rev.
Cutting depth a_p	0.5 - 8 mm
Chip breaker	SM

Corner radius	1.2 mm
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide
ISO code indexable insert	CNMG 120412
Number of changes/inserts	4
Tolerance	M
Type of product	Indexable insert for turning