



Seaming tool, Jaw capacity: 130mm



Order data

Order number	861620 130
GTIN	
Item class	83K

Description

Version:

Manual vacuum pumps for maximum suction force, and hence very high horizontal clamping force. Levers on the guide rails to compensate for differences in height. A few strokes of the pump are sufficient to generate the necessary underpressure. A marking ring on the pump tappet allows the vacuum to be checked at any time. Further pumping brings the vacuum back to the maximum.

Application:

For clamping and positioning components with smooth surfaces, such as ceramic, granite, Corian®, plastic, sheet metal and glass.

Note:

The seaming tool should be released for storage, so that the rubber cups do not deform permanently.

See No. 086200 for suction lifters.

Technical description

Jaw capacity	130 mm
maximum clamping force	1200 N
overall length	715 mm
Weight	4.08 kg
Width	215 mm
Type of product	Clamp

