

**Garant**
**CNMM 160616, Grade: HB7010-1**


### Order data

Order number	250460 HB7010-1
GTIN	4045197779793
Item class	21G

### Description

CNMM 160616 HB7010-1 Grade: HB7010-1  
 Chip breaker: SR  
 Cutting depth  $a_p$ : 2 - 10 mm  
 Feed  $f$ : 0.4 - 1.2 mm/rev.  
 Cutting speed  $v_c$  main application: 100 - 375 m/min

### Technical description

Corner radius	1.6 mm
Feed $f$	0.4 - 1.2 mm/rev.
Cutting speed $v_c$ main application	100 - 375 m/min
Chip breaker	SR
Main application	P
Cutting conditions	continuous
Grade	HB7010-1

Cutting depth $a_p$	2 - 10 mm
Finishing/roughing assignment	Roughing
Tool material	Carbide
ISO code indexable insert	CNMM 160616
Number of changes/inserts	4
Type of product	Indexable insert for turning