

**Garant****DNMG 110408, Grade: HB7010-1**

## Order data

Order number	250754 HB7010-1
GTIN	4045197779878
Item class	21G

## Description

DNMG 110408 HB7010-1 Grade: HB7010-1  
Chip breaker: SM  
Tolerance: M  
Cutting depth  $a_p$ : 0.5 - 5 mm  
Feed  $f$ : 0.2 - 0.5 mm/rev.  
Cutting speed  $v_c$  main application: 120 - 440 m/min

## Technical description

Chip breaker	SM
Cutting speed $v_c$ main application	120 - 440 m/min
Cutting conditions	continuous
Feed $f$	0.2 - 0.5 mm/rev.
Corner radius	0.8 mm
Cutting depth $a_p$	0.5 - 5 mm

Main application	P
Grade	HB7010-1
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide
ISO code indexable insert	DNMG 110408
Number of changes/inserts	4
Tolerance	M
Type of product	Indexable insert for turning