

Garant**DNMG 150604, Grade: HB7010-1**

Order data

Order number	250760 HB7010-1
GTIN	4045197779885
Item class	21G

Description

DNMG 150604 HB7010-1 Grade: HB7010-1
Chip breaker: SM
Tolerance: M
Cutting depth a_p : 0.5 - 5 mm
Feed f : 0.2 - 0.5 mm/rev.
Cutting speed v_c main application: 120 - 440 m/min

Technical description

Feed f	0.2 - 0.5 mm/rev.
Corner radius	0.4 mm
Cutting speed v_c main application	120 - 440 m/min
Grade	HB7010-1
Main application	P
Cutting depth a_p	0.5 - 5 mm

Chip breaker	SM
Cutting conditions	continuous
Finishing/roughing assignment	Semi-roughing
Tool material	Carbide
ISO code indexable insert	DNMG 150604
Number of changes/inserts	4
Tolerance	M
Type of product	Indexable insert for turning