

**Garant****Indexable insert for turning KNUX 160405R, for medium machining****Order data**

Order number	251030 HB7010-1
GTIN	4045197779939
Item class	21G

**Technical description**

Main application	P
Corner radius	0.5 mm
Chip breaker	SM
Type	HB7010-1
Feed f	0.2 - 0.5 mm/rev.
Cutting depth $a_p$	0.5 - 5 mm
Cutting speed $v_c$ main application	120 - 440 m/min
Chip diverter	2.2 mm
Cutting conditions	continuous
Finishing/roughing assignment	Semi-roughing
Tool material	Carbide
Number of changes/inserts	2
ISO code indexable insert	KNUX 160405R
Type of product	Indexable insert for turning

