

Garant
SNMG 120408, Grade: HB7010-1


Order data

Order number	251144 HB7010-1
GTIN	4045197780027
Item class	21G

Description

SNMG 120408 HB7010-1 Corner radius: 0.8 mm
 Grade: HB7010-1
 Chip breaker: SS
 Cutting depth a_p : 0.3 - 2 mm
 Feed f : 0.1 - 0.4 mm/rev.
 Cutting speed v_c main application: 150 - 500 m/min

Technical description

Main application	P
Cutting speed v_c main application	150 - 500 m/min
Feed f	0.1 - 0.4 mm/rev.
Cutting conditions	continuous
Chip breaker	SS
Grade	HB7010-1
Corner radius	0.8 mm

Cutting depth a_p	0.3 - 2 mm
Finishing/roughing assignment	Finishing
Tool material	Carbide
ISO code indexable insert	SNMG 120408
Number of changes/inserts	8
Type of product	Indexable insert for turning