


Garant
SNMG 120412, Grade: HB7010-1

Order data

Order number	251226 HB7010-1
GTIN	4045197780058
Item class	21G

Description

SNMG 120412 HB7010-1 Corner radius: 1.2 mm
 Grade: HB7010-1
 Chip breaker: SM
 Cutting depth a_p : 0.5 - 6 mm
 Feed f : 0.15 - 0.5 mm/rev.
 Cutting speed v_c main application: 120 - 440 m/min

Technical description

Cutting conditions	continuous
Cutting speed v_c main application	120 - 440 m/min
Cutting depth a_p	0.5 - 6 mm
Feed f	0.15 - 0.5 mm/rev.
Corner radius	1.2 mm
Grade	HB7010-1
Chip breaker	SM

Main application	P
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide
ISO code indexable insert	SNMG 120412
Number of changes/inserts	8
Type of product	Indexable insert for turning