


Garant
SNMG 150612, Grade: HB7010-1


Order data

Order number	251232 HB7010-1
GTIN	4045197780072
Item class	21G

Description

SNMG 150612 HB7010-1 Corner radius: 1.2 mm
 Grade: HB7010-1
 Chip breaker: SM
 Cutting depth a_p : 0.5 - 6 mm
 Feed f : 0.15 - 0.5 mm/rev.
 Cutting speed v_c main application: 120 - 440 m/min

Technical description

Cutting conditions	continuous
Chip breaker	SM
Main application	P
Corner radius	1.2 mm
Feed f	0.15 - 0.5 mm/rev.
Grade	HB7010-1
Cutting speed v_c main application	120 - 440 m/min

Cutting depth a_p	0.5 - 6 mm
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide
ISO code indexable insert	SNMG 150612
Number of changes/inserts	8
Type of product	Indexable insert for turning