

Garant
SNMG 120408, Grade: HB7010-1


Order data

Order number	251324 HB7010-1
GTIN	4045197780102
Item class	21G

Technical description

Chip breaker	SG
Cutting speed v_c main application	100 - 375 m/min
Feed f	0.25 - 0.8 mm/rev.
Main application	P
Cutting conditions	continuous
Grade	HB7010-1
Cutting depth a_p	1.5 - 9 mm
Corner radius	0.8 mm
Finishing/roughing assignment	Roughing
Tool material	Carbide
ISO code indexable insert	SNMG 120408

Number of changes/inserts	8
Type of product	Indexable insert for turning