

**Garant**
**SNMG 120412, Grade: HB7010-1**


### Order data

Order number	251326 HB7010-1
GTIN	4045197780119
Item class	21G

### Technical description

Grade	HB7010-1
Cutting conditions	continuous
Cutting speed $v_c$ main application	100 - 375 m/min
Corner radius	1.2 mm
Cutting depth $a_p$	1.5 - 9 mm
Chip breaker	SG
Main application	P
Feed $f$	0.25 - 0.8 mm/rev.
Finishing/roughing assignment	Roughing
Tool material	Carbide
ISO code indexable insert	SNMG 120412

Number of changes/inserts	8
Type of product	Indexable insert for turning