

Garant
SNMM 120412, Grade: HB7010-1


Order data

Order number	251386 HB7010-1
GTIN	4045197780164
Item class	21G

Technical description

Corner radius	1.2 mm
Feed f	0.4 - 1.2 mm/rev.
Grade	HB7010-1
Cutting depth a_p	2 - 12 mm
Cutting speed v_c main application	100 - 375 m/min
Cutting conditions	continuous
Main application	P
Chip breaker	SR
Finishing/roughing assignment	Roughing
Tool material	Carbide
ISO code indexable insert	SNMM 120412

Number of changes/inserts	8
Type of product	Indexable insert for turning