

Garant
SNMM 150616, Grade: HB7010-1


Order data

Order number	251390 HB7010-1
GTIN	4045197780171
Item class	21G

Description

SNMM 150616 HB7010-1 Corner radius: 1.6 mm
 Grade: HB7010-1
 Chip breaker: SR
 Cutting depth a_p : 2 - 12 mm
 Feed f : 0.4 - 1.2 mm/rev.
 Cutting speed v_c main application: 100 - 375 m/min

Technical description

Cutting conditions	continuous
Main application	P
Chip breaker	SR
Cutting speed v_c main application	100 - 375 m/min
Cutting depth a_p	2 - 12 mm
Feed f	0.4 - 1.2 mm/rev.
Corner radius	1.6 mm

Grade	HB7010-1
Finishing/roughing assignment	Roughing
Tool material	Carbide
ISO code indexable insert	SNMM 150616
Number of changes/inserts	8
Type of product	Indexable insert for turning